


013140230

Aluminium Enclosure Standard
313 x 404 x 227 mm

Aluminium Enclosure Standard 313 x 404 x 227 mm

Catalogues | Declaration of Conformity | Drawing | 3D Data | Assignmentplan | Terminal Mounting

Technical data

Height	313 mm
Width	404 mm
Depth	227 mm
Material	Aluminium
Material quality	DIN EN 1706 EN AC-AlSi 12 (Fe)
Colour	Silver gray (RAL 7001)
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-30 °C
temperature max.	80 °C
Seal material	PU (polyurethane) (standard)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV, SBG, SWB, SBGL
Special colours on request	Yes
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tarif number	85369095
Weight	10 kg
GTIN	4250157900418


ETIM classification

ETIM 8	EC000058

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories



100110200
Mounting plate for 01.314011



100220010
HINGE INTERNAL / STEEL



100270010
HINGE EXTERNAL / GREY



100311020
Outer bracket fastening set M6



100614270
DIN rail 35/7,5 for xx.234011



100620110
Earth rail for 01.234011