



Main

Enclosure type	Weatherproof enclosure
Range of product	Kaedra
Device short name	Kaedra versatile enclosure

Complementary

Enclosure mounting	Surface
Type of front cover	Transparent
Number of horizontal rows	1
Number of 18 mm modules per row	12
Total number of 18 mm modules	12
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Locking options description	Optional keylock
Enclosure material	Plastic
Width	340 mm
Height	335 mm
Depth	160 mm
Colour	Door : transparent green Enclosure : light grey (RAL 7035)

Environment

Standards	EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 670
Fire resistance	750 °C
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Electrical shock protection class	Class II
Ambient air temperature for operation	-25...60 °C
RoHS EUR conformity date	0622
RoHS EUR status	Compliant