

M12 HB2.5

M12™ HIGH OUTPUT™ 2.5 AH BATTERY

- The new M12™ 2.5 Ah HIGH OUTPUT™ battery pack provides up to 25% more the power vs M12 B2 REDLITHIUM™ battery pack
- Runs up to 25% cooler than other M12™ REDLITHIUM™ battery packs through heavy applications
- Sophisticated electronics: REDLINK™ intelligence
- Overload protection prevents user from damaging their cordless power tool investment in abusive situations
- Temperature management system keeps battery in ideal temperature range to provide maximum life
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- Discharge protection prevents cell damage from over-discharge
- *Compared with other Lithium -Ion technologies and / or with previous MILWAUKEE® battery technology. Results dependent on voltage, tool and application
- Integrated welded frame battery construction with shock responsive separators preventing pack failure from excessive vibrations or drops
- Can be used in extreme temperatures down to -20 °C without compromising on run time and battery life
- Discharge protection prevents cell damage from over-discharge
- Improved housing is resistant to oils, solvents and greases



REDLITHIUM™

Battery pack capacity (Ah)	2.5
Charge time C12 C charger	55 min
Charge time M12 C4 charger	55 min
Charge time M12_18 C charger	55 min
Charge time M12_18 FC charger	40 min
Weight (kg)	
Article number	4932480164

