

FEATURES

- Range: 0-100mm
- Resolution: 0.01mm
- 80mm Dial face
- Anvil thread M2.5mm
- Stem diameter: 8mm

RS PRO Metric Dial Indicator, 0 - 100 mm Measurement Range, 0.01 mm Resolution

RS Stock No.: 180-9468



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Data Sheet



_		_	
Prod	lict	Descri	ıntını
1 100	uot	Desci	IPLIOI

Adjustable dial.

Bezel lock.

Flat back fitting.

Fitted with ball anvil.

Hardened & ground racks.

General Specifications

Maximum Measurement	100mm
Resolution	0.01 mm
Zero Resettable	Yes
Measurement Range	0 - 100 mm
Imperial or Metric	Metric

Mechanical Specifications

Electrical Specifications

Protection Category

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	
Hazardous Area Certification	
Standards Met	

Data Sheet



Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories