

## Data sheet

Commercial Art.No.: R1.190.0060.0

PLC digital I/O-module SP-SDI8-P1-K-C DC 24V

samosPRO, IN-module with 8 input, push-in clamp terminal pluggable



Commercial Art.No.	R1.190.0060.0
EAN	4046521309648
Order Unit	1

Certificates / Approvals



## Technical data

### General

SIL according to IEC 61508	3
In-/outputs configurable	Yes

### Connection Data

Type of electric connection	Spring clamp connection
-----------------------------	-------------------------

### Output circuit

Number of outputs	0
-------------------	---

### Other

Suited for safety functions	Yes
Type of supply voltage	DC
Type of voltage (input voltage)	

### Control circuit

Number of inputs	8
Input current (at state "1")	8 mA
Permitted voltage at input	30 V

### Supply circuit

Min. supply voltage at DC	16.8 V
---------------------------	--------

Max. supply voltage at DC	30 V
---------------------------	------

**Dimensions**

Depth	121 mm
Width	22.5 mm
Height	96.5 mm

**Classification**

ECLASS 8.1	27242204
ETIM 7.0	EC001419
ETIM 6.0	EC001419
ETIM 5.0	EC001419
ETIM 4.0	EC001419
ETIM 3.0	EC001419

**Safety parameters**

Category (ISO 13849-1)	4
PL (ISO 13849-1)	Level e
SIL <sub>CL</sub> (IEC 62061)	3
HFT	1
T <sub>M</sub>	20 a
Note	More safety characteristics can be found in the manual.