



mecalectro

Shotbolts for general use – 8.10.BJ.28



Locking mode: Power off

Stroke: 13 mm

Shearing strength: 60 daN

Return force: 0.1 daN

Consumption: 9W

Total mass: 350 g

Degree of protection / Energetic class: IP 40 / B

Standard supplies: 24 - 48Vcc

Possible supplies: From 12 to 205Vcc

Bolt position monitoring : No

Standard: NF C 79-300

Examples of applications: Locking for automated machines, indexing for drink dispensers, tickets...