



### Main

Range	Acti 9
Product name	Lineryg FH
Product or component type	Connector
Accessory / separate part category	Connection accessory
Poles description	3P + N
Quantity per set	Set of 4
Comb busbar and distribution block compatibility	Monoconnect

### Complementary

[In] rated current	100 A
Colour	White (RAL 9003)
Connections - terminals	Screw clamp terminals top connector35 mm²
Tightening torque	4 N.M
Range compatibility	Acti9 iC60 comb busbar Acti9 iK60 comb busbar Acti 9 iDPN comb busbar Acti9 iDPN Vigi comb busbar Acti9 iID comb busbar Acti9 iID K comb busbar Acti9 iSW comb busbar Acti9 iSW-NA comb busbar Acti9 STI comb busbar

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	64 G
Package 1 Height	2.9 Cm
Package 1 width	6.1 Cm
Package 1 Length	7.9 Cm
Unit Type of Package 2	S02
Number of Units in Package 2	100
Package 2 Weight	6.569 Kg
Package 2 Height	15 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	Commercialised
-----------------------	----------------