

Ha-EIZ4 RJ45S-0.5M/KETH



Image is for illustration purposes only. Please refer to product description.

Part number	72 MD M4R M400 5K
Specification	Ha-EIZ4 RJ45S-0.5M/KETH
HARTING eCatalogue	https://harting.com/72MDM4RM4005K

Identification

Category	System cabling
Series	RJ45 Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	RJ45
Connector 2	M12 D-coding Male
Type of cable	Copper cable (round)

Version

Cable length	0.5 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +80 °C

Material properties

Material (cable)	PVC
------------------	-----



Pushing Performance
Since 1945

Material properties

Colour (cable) Green

Specifications and approvals

Approvals CE

PROFINET Yes

Commercial data

Packaging size 1

Country of origin China

European customs tariff number 85444290

GTIN 5713140268203

eCl@ss 27060390 Ready-made data cable (unspecified)

ETIM EC002599
