

Datasheet

Chassis Mount Power Line Filter, with Tab Terminals

RS Stock number 240-258



Specifications:

S/N	Rated Current (A) (40°C)	Max. leakage current (mA) (250V, 50Hz)	L (mH)	Cx (μF)	Cy (pF)	Weight (g)
240258	3	0.5	4 x 1	0.1	4700	240
240264	6	0.5	4 x 0.45	0.1	4700	240
240270	10	0.5	4 x 0.2	0.1	4700	240

Operating Voltage: 420VAC
 Operating Frequency: 0 – 400Hz
 Temperature Range: -25°C - +85°C

