



Fuse base, low voltage, 1250 A, AC 690 V, NH4, 1P, IEC, screw mounting



Part no. **NH4 SINGLE POLE 1250A**
Catalog No. **SD4-S**

Similar to illustration

Delivery program

Product range			Fuse accessory
Basic function			Fuse-base
Field of application			low voltage
Rated current	I	A	1250
Rated voltage			AC 690 V
Construction size			NH4
Description			screw mounting
Number of poles			1P
Standard/Approval			IEC
Material			Thermoplastic body
Standards/Regulations			IEC 60269-1
Optional accessories			clip-in phase barriers terminal shrouds fuse-covers microswitch IP20 finger-safe protection kits neutral links phase barriers

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse base (EC000067)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC fuse base (ecI@ss10.0.1-27-14-21-06 [AKE278013])			
Construction size			NH4
Number of poles			1
Rated current		A	1250
Bus-mounting type			No
Swivelling mechanism			No