



 PRODUCT-DETAILS

S25/25/C

STR NPB ENTRY BUSH 25MM-MET



General Information

Extended Product Type	S25/25/C
Product ID	7TCA296010R0091
EAN	5020963003561
Catalog Description	STR NPB ENTRY BUSH 25MM-MET
Long Description	Nickel Plated Brass Smooth Entry Bushing, Hole Size-25mm

Additional Information

Product Main Type	ADAPTAFLEX FLEXIBLE CABLE PROTECTION
Application	For Locking Conduit Into Plain Holes in Enclosures

Ordering

EAN	5020963003561
UPC	786210261577

Technical

Number of Batteries	0
Color	Metallic
Material	Brass
Size	25mm

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963003561
Package Level 1 Height	9.84 in 250 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001180 - Screw connection for protective metallic hose
ETIM 9	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121312

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

