

PVC Cable	No. of Cond.	AWG	Jacket Characteristics	ID Number	Ship Wt. (lbs)	Cond. Colors	Shield	UL	CSA	Type	MSHA	Temp. (°C)
	4	18	7.2 mm OD, PVC, YE, 300 V	RF50579-30M RF50579-100M RF50579-200M	6 18 36	BK, BU, WH, BN		•	•	AWM 2517	•	105° -40°
	4	18	7.2 mm OD, PVC, GY, 300 V	RF50580-30M RF50580-100M RF50580-200M	6 18 36	BK, BU, WH, BN		•	•	AWM 2517	•	105° -40°
	4	18	7.2 mm OD, PVC, BK, 300 V	RF50816-30M RF50816-100M RF50816-200M	6 18 36	BK, BU, BN, WH		•	•	AWM 2517	•	105° -40°
	4	18	7.2 mm OD, PVC, YE, 600 V	RF50844-30M RF50844-100M RF50844-200M	6 17 34	BK, BU, WH, BN		•	•	ITC/PLTC AWM 2586		105° -30°
	4	24	3.8 mm OD, PVC, YE, 300 V	RF51255-30M RF51255-100M RF51255-200M	2 6 11	BN, BK, BU, WH		•	•	AWM 2103		105° -40°
	4	26	4.4 mm OD, PVC, BK, 300V	RF50870-30M RF50870-100M RF50870-200M	3 9 17	BN, WH, BU, BK		•	•	AWM 2517		105° -40°
	4	22	5.7 mm OD, PVC, YE, 300 V	RF50656-30M RF50656-100M RF50656-200M	4 13 25	GN, RD, RD/BK, RD/WH	Braid	•	•	AWM 20838		105° -40°
	4	22	5.1 mm OD, PVC, GY, 300 V	RF50773-30M RF50773-100M RF50773-200M	3 9 18	WH, BK, BN, BU, Drain (22)	Foil Drain	•	•	ITC/PLTC AWM 2517		105° -30°
	4	22	5.1 mm OD, PVC, GY, 300 V	RF50577-30M RF50577-100M RF50577-200M	3 9 18	BN, WH, BU, BK, Drain (22)	Foil/Drain	•	•	AWM 2517		105° -40°
	4	22	5.1 mm OD, PVC, BK, 300 V	RF50805-30M RF50805-100M RF50805-200M	3 9 18	BN, WH, BU, BK, Drain (22)	Foil/Drain	•	•	AWM 2517		105° -40°
	4	22	7.2 mm OD, PVC, GY, 300 V	RF50729-30M RF50729-100M RF50729-200M	5 17 33	BN, WH, BU, BK, Drain (22)	Foil/Drain Braid	•	•	AWM 2517		105° -40°
	4	22	7.2 mm OD, PVC, GY, 300 V	RF50823-30M RF50823-100M RF50823-200M	5 17 33	BN, WH, BU, BK, Drain (22)	Foil/Drain Braid	•	•	ITC/PLTC AWM 2517		105° -30°
	4	22	5.1 mm OD, PVC, GY, 300 V	RF50516-30M RF50516-100M RF50516-200M	3 9 18	BN, WH, BU, BK		•	•	AWM 2517	•	105° -40°
	4	22	5.1 mm OD, PVC, YE, 300 V	RF50530-30M RF50530-100M RF50530-200M	3 9 18	BN, WH, BU, BK		•	•	AWM 2517	•	105° -40°
	4	22	5.7 mm OD, PVC, YE, 300 V	RF50555-30M RF50555-100M RF50555-200M	4 11 22	RD/BK, RD/WH, RD, GN		•	•	AWM 2517	•	105° -40°
	4	22	5.1 mm OD, PVC, BU, 300 V	RF50598-30M RF50598-100M RF50598-200M	3 9 18	BN, WH, BU, BK		•	•	AWM 2517	•	105° -40°
	4	22	5.3 mm OD, PVC, GY, 300 V	RF50698-30M RF50698-100M RF50698-200M	3 9 18	BN, WH, BU, BK		•	•	ITC/PLTC AWM 2517		105° -30°
	4	22	5.7 mm OD, PVC, GY, 600 V	RF50914-30M RF50914-100M RF50914-200M	3 10 20	BN, WH, BU, BK		•	•	AWM 2586		105° -40°
	4	22	5.2 mm OD, PVC, BK, 300 V	RF50983-30M RF50983-100M RF50983-200M	3 9 18	BN, WH, BU, BK		•	•	AWM 2517	•	105° -40°
	4	24	4.4 mm OD, PVC, YE, 300 V	RF50822-30M RF50822-100M RF50822-200M	2 7 14	BN, WH, BU, BK		•	•	AWM 2517 CL2		105° -30°
	4	26	3.2 mm OD, PVC, BK, 300 V	RF50590-30M RF50590-100M RF50590-200M	1 4 7	WH, BN, BU, BK						105° -40°