

Planer XGT®

KP001G

40Vmax • 82 mm

XGT® Battery powered planer for heavy duty use.

Makita's KP001G is a tool made for professionals. It has Increased cutting depth and shiplapping depth. The Compact design and good grip are made to reduce operator fatigue. The Auto-start Wireless System (AWS) connects to vacuum cleaner with Bluetooth.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	15000 min ⁻¹
Planing Width	82 mm
Chip Thickness (Planing Depth)	0 - 4 mm
Max. Shiplapping Depth	25 mm
AWS ready	✓
Sound Power Level (L _{WA})	98 dB(A)
Sound Pressure Level (L _{pA})	90 dB(A)
Product net weight	2,5 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,7 - 4,9 kg
Product Dimensions (L x W x H):	385 x 156 x 166 mm

User benefits

- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low
- The front of the base has 3 grooves for making chamfers.
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- Chip ejection can be directed to either side of the tool

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing