



R-068

Fully coated safety gloves designed for impact, cut and liquid protection



Impact

Abrasion Protection



Cut

Liquid Spray and Splash



Oil



Light Duty

Fully coated safety gloves designed for impact, cut and liquid protection

- **Advanced defenses:** Developed with F3 Technology™, RINGERS® R068 impact gloves feature a comfortable, dexterous TPR (thermoplastic rubber) design, offering optimal hand coverage
- **Specialized protection:** These hand protection gloves boast fully dipped nitrile coating, granting wearers an effective liquid resistance barrier, for truly reliable personal protection
- **Enhanced features:** Their high-visibility design reinforces wearer protection, while touchscreen-compatible thumb tips, index and middle fingers enable technological interaction without compromising hand safety
- **Strengthened grip:** RINGERS® R068 safety gloves also feature half-dipped palm coating with a sandy finish, offering better grip on wet and dry surfaces, for improved workplace safety



Industries

- Construction
- Oil and gas
- Manufacturing
- Mining
- Automotive Aftermarket
- Chemical
- Emergency Medical Services
- Machinery and Equipment
- Metal fabrication

Applications

- Running tools into the wellbore
- Assembly and disassembly of large pipes
- Engagement and release of drill string slips
- Unloading and stacking pipe
- Set-up of pressure manifold and tubing injector head
- General pumping work
- Loading and hauling
- Assembling and mounting components
- Concentration mixing and palletisation
- Hydraulic repair
- Use of binding agents
- Smelting and cleaning of equipment
- Re-fuel oil fluid and diesel
- Tank Cleaning



R-068

Fully coated safety gloves designed for impact, cut and liquid protection

Key Features

- **Patented TPR design:** For PPE gloves with strong impact protection
- **Fully dipped nitrile coating:** Liquid resistance and hand protection
- **Touchscreen compatibility:** For consistent protection and usability

Technologies



Touchscreen Compatible

Performance Standards & Regulatory Compliance



4X44FP

ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



X1XXXX

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COATING COLOR	PACKAGE
RINGERS® R068	Finishing: Fully Dipped Coating Material: Nitrile Liner Material: HPPE Cuff Style: Knitwrist	13	8, 9, 10, 11, 12, 13	Red	10 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

