



PW3 HI-VIS WORK TROUSERS

DESCRIPTION

Constructed using premium HiVisTex Pro tape and durable polyester/cotton fabric, this contemporary Hi-Vis Work Trousers provides ultimate wearer comfort. Oxford fabric reinforcement at key abrasion points and triple stitching throughout guarantees maximum durability. This trouser features top loading kneepad pockets and an easy access multiway thigh pocket for secure storage of your phone, keys and tools.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester, 600D Oxford, PU Coated, 210g**
-  **Orange/Black Short 28-42**

FEATURES

- Durable polycotton fabric with Texpel stain resistant finish
- Texpel™ Stain Eco a premium stain resistant finish to repel grime and water
- High rise back waistband ensures protection in all working positions
- Easy access cargo pocket
- Extendable leg length (31" to 33")
- Free pair of kneepads included with this trouser
- Triple-stitched seams for extra durability
- 2 Side pockets
- Two back patch pockets
- Double rule pocket
- D-ring for keys or ID cards
- Hammer loop for secure storage of work tools

STANDARDS

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)
ANSI/ISEA 107 SUPPLEMENTAL CLASS E

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
PW340OBS	ORANGE/BLACK	28-9

FEATURES



TOP-LOADING KNEE PAD POCKETS
Top-loading knee pad pockets for quick and easy access



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



HEAT APPLIED SEGMENTED REFLECTIVE TAPE
This symbol indicates that the garment has heat applied reflective tape



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements



PERFORMANCE WORKWEAR
PW3™ contemporary workwear blends
sports and lifestyle trends with function,
a modern fit and improved comfort.

GET THE
COLLECTION



TECHINCAL INFORMATION



SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777) Bracetown
Business Park Clonée Dublin 15 D15 YN2P, Ireland
Cert No: 2777/14048-03/E00-00

· Wash garment inside out and fully
fastened

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
PW340OBS28	Orange/Black	65	45	36	.934	5850.000	5036108312993	15036108801357
PW340OBS30	Orange/Black	65	45	36	.968	5850.000	5036108313006	15036108801364
PW340OBS32	Orange/Black	65	45	36	.979	5850.000	5036108313013	15036108801371
PW340OBS33	Orange/Black	65	45	36	.986	5850.000	5036108313020	15036108801388
PW340OBS34	Orange/Black	65	45	36	.995	5850.000	5036108313037	15036108801395
PW340OBS36	Orange/Black	65	45	36	.998	5850.000	5036108313044	15036108801401
PW340OBS38	Orange/Black	65	45	36	1.027	5850.000	5036108313051	15036108801418
PW340OBS40	Orange/Black	65	45	36	1.054	5850.000	5036108313068	15036108801425
PW340OBS41	Orange/Black	65	45	36	1.060	5850.000	5036108313075	15036108801432
PW340OBS42	Orange/Black	65	45	36	1.079	5850.000	5036108313082	15036108801449