

Datasheet

ECP-18 Series

18w Multi Head Plug In Power Supply



Features

- Universal input
- No load power consumption
- Compact and light-weight plastic case
- Protections: Short circuit/ Overload
- Class II power supply (without earth pin)
- Pass LPS
- 1 Year warranty

Model				...	
Input	Input Voltage Range	100-240VAC			
	Input Frequency Range	47Hz to 63Hz			
	No Load Power Consumption	0.3W Max			
	In-Rush Current	50A Max			
	Input Current	0.8A Max			
Output	Output Voltage		+12V	+15V	+24V
	Output Load Range		0.01-1.5A	0.01-1.2A	0.01-0.75A
Environment	Efficiency	≤83%			
	Working Temperature	0°C-40°C			
	Working Humidity	10%-95%			
Safety	EMI	EN55022 (EN61000-3-2, EN61000-3-3)			
	EMC	EN55024 (IEC61000-4-2, IEC61000-4-3, IEC61000-4-4, IEC61000-4-5)			
Dimensions	Size	86x 56x 38mm			

UNIT: mm

