

Features

- DPDT
- Momentary
- Solder Tags or PC Tags

RS PRO DPDT Push Button Switch

RS Stock No.: 0856840



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Metal plunger foot switches with a high operating force making them ideal for various foot control applications.

General Specifications

Switch Type	Push Button
Switch Operation	Momentary
Termination	Solder or PC Tags

Mechanical Specifications

Operating Temperature	-20°C to +65°C
-----------------------	----------------

Electrical Specifications

Rating	AC 125V 4A, 250V 2A
Contact Resistance	50mΩ max
Insulation Resistance	DC 500V 100MΩ min
Dielectric Strength	AC 500V 1 minute
Electrical Life	50,000 cycles at full load

Approvals

Standards Met	RoHS
---------------	------

Similar Products

Stock No.	Brand	Product Name	Termination
0856840	RS PRO	Pushbutton Switch	Solder Tags
0856841	RS PRO	Pushbutton Switch	PC Tags

