



Rotary Hammer LXT®

DHR182

18V • SDS-PLUS • 18 mm • 1.7 J

Lightweight and handy brushless rotary hammer for professional use

Lightweight and powerful brushless rotary hammer with AVT vibration absorber for SDS-PLUS bits. Drilling can be done with or without impact. Adjustable operating speed 0-1350 min⁻¹. The device creates 1.7J impact force and the maximum capacity in concrete is 18mm.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Impact Energy	1,7 J
Optimum Drilling Diameter Range in Concrete	3,2 - 10 mm
Max. Drilling Diameter in Concrete	18 mm
Max. Drilling Diameter in Wood	24 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 5000 min ⁻¹
No load speed	0 - 1350 min ⁻¹
Drilling diameter with TCT core bit	35 mm
Adapted for SDS-PLUS bits	✓
AWS ready	✓
Tool weight with battery	2,4 - 3,2 kg

User benefits

- Brushless maintenance-free and long-life motor
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Reversing switch
- Ergonomic chassis design ensures a good working position.
- LED light illuminates the work site
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

■ Optional AC

199664-6
Dust collection system



821552-6
Makpac case (4)



839891-0
Inner tray (4)



■ Other

User manual

Parts drawing