

Heavy-duty workbench 2182 m - 13 drawers - Wooden worktop - high version



Description:

- Description:
- One 6-drawer unit JLS2-MBS6T: - 4 drawers 60 mm high, 1 drawer 130 mm high, 1 drawer 270 mm high.
- One 7-drawer unit JLS2-MBS7T: - 5 drawers 60 mm high, 1 drawer 130 mm high, 1 drawer 200 mm high. - Drawer useful size: L.569 x D.421mm. - Single keylock. - Fitted with 4 jack-mounted swivel feet for perfect adjustment. - Overall dimensions: L.722 x D.701 x H.810 mm.
- 1 JLS2-PSH foot: - Foot made of epoxy painted sheet steel (thickness 12/10ths). - Fitted with jack-mounted swivel feet for adjustment providing complete stability irrespective of the type of floor. - Dimensions: L.100 mm x H.985 mm x D.650 mm. - Colour black 9004.
- 1 low unit raising base JLS2-BASEMBS: - Base in 12/10th steel sheet. - Dimensions: L.720 mm x H.180 mm x D.699 mm. - Colour black 9004.
- A wooden worktop JLS2-PB3 - Depth 750mm, thickness 40 mm ensuring resistance and durability. - Linseed oil treatment for improved resistance to liquids and ease of maintenance. Capable of supporting loads: 1 ton.
- A JLS2-TRBB3 cross-beam - Multifunction cross beam: connecting, reinforcement and storage space, 2 possible positions: horizontal or

vertical. - Made of epoxy painted steel sheet (thickness 12/10ths). - Colour red 3020.

	Depth [mm]	Length L [mm]	Height H [mm]	Weight [Kg]
JLS2-2MW13DH	750.0	2182.0	850.0	249.6