	WD CON	FIDENTIAL		
iiiD	My Cloud [™] Home Personal Cloud Storage	Duo		
Product Specifications	Average latency	n/a		
	Average read seek	n/a		
	Battery	No		
	Max Capacity	6TB		
	Drive Bays	2		
	Interfaces	Gigabit Ethernet		
	Memory	1GB DDR3L 32bit (256M x 16bit x 2pcs)		
	Processor		Realtek RTD1296PB-CG 1.4Ghz A53 Quad Core	
Product Dimensions	Length	6.30 in or 160 mm		
	Width	3.94 in or 100 mm	3.94 in or 100 mm	
	Height	7.09 in or 180 mm	7.09 in or 180 mm	
	Weight:			
	6TB	5.27 lbs or 2.39 kg		
olors available		White		
country Code / Origin		Product of Thailand or Produc	Product of Thailand or Product of Malaysia	
Environmental Specifications	Operating Temperature	5° C to 35° C (41° F to 95° F)		
	Non-op Temperature	-20° C to 65° C (-4° F to 149°	F)	
	Operating Relative Humidty	20%~80%	20%~80%	
	Non-op Relative Humidity	5%~90%		
Power Specifications	AC input voltage (AC adapter)	90-260 VAC		
	AC input frequency	47-63 Hz	47-63 Hz	
	DC output	Up to 12TB (12VDC, 3A), 16T	Up to 12TB (12VDC, 3A), 16TB+ (12VDC, 4A)	
anguages for User Manual		Chinese, Traditional Czech Danish Dutch English Finnish French German Greek Hungarian Arabic Chinese, Simplified	 Japanese Korean Norwegian Polish Portuguese Russian Slovakian Spanish Swedish Turkish Italian Indonesian (Bahasa) 	
		 Chinese, Traditional Czech Danish Dutch English Finnish French German Greek Hebrew 	 Korean Norwegian Polish Portuguese Russian Slovakian Spanish Swedish Turkish 	
imited Warranty ²	Worldwide	2 years		
Previous Product Model	Product Name	My Cloud Home Duo		
	Ref Order Number	WDBMUT		
Regulatory	NRCAN compliant	Yes		
	ROHS compliant ¹	Yes		
oftware included		None		