

Professionally approved products.

Product datasheet

COBASwitch - Purpose-designed switchboard matting

- Size: 0.9m x 2m RS Code: 4716254
- Product Height: 9mm
- Material: Natural rubber base Polymer
 - Provides safety for operatives against electrical shocks.
 - For use in front of switchboards and high voltage equipment.
 - Slip-resistant fine fluted surface.
 - 9.5mm tested to 15,000 volts for 650 volt rated working.
 - 9.5mm conforms to BS921/1976.
- Surface Finish: 2mm high ribbed pattern providing safe working with standard 3 phase 450-volt working.
- Tensile Strength: 5 MPA
- Elongation: 250%
- Compression Set (22h@700 C): -28°C
- Change in Hardness +2 IRHD
- Change in Tensile -8%
- Change in Elongation -12%
- Dielectric Strength 5KV/mm
- Electrical Breakdown Strength 11KV minimum
- Leakage Current 160mA/m² max
- Weight 10kg/m² approx.
- Environmental Resistance: Use in dry areas.
- UV Resistance: Yes
- Typical Applications: Suitable for use in high voltage areas. Specifically designed for use in front of open switchboards or high voltage equipment. Product ensures safety for operators against electrical shocks. Tested to 11,000 volts for 450 volt working.
- Installation Method: Loose lay





