

## USB 3.1



### Store and access your data anywhere.

Take your data on-the-go with the SL200 Portable SSD from Lexar. This sleek and slim drive features a premium finish and is available in 512GB, 1TB, 2TB, 480GB and 960GB of storage space. To keep your data secure, it's drop-, shock-, vibration-resistant and comes with an advanced security solution with 256-bit AES encryption. Performance-wise, it has transfer speeds of up to 550 MB/s and a write speed of up to 400 MB/s<sup>1</sup>. Connect it to your system using the included USB Type-C to USB Type-C or USB Type-C to Type-A cable, and it's ready to use.



Performance



Portability



Durability



Protection

#### Product Highlights:

- SSD-level performance – with speeds up to 550MB/s read and 400MB/s write<sup>1</sup>
- Sleek, slimline styling with a premium finish
- Durable, portable design—resists harsh temperatures and vibration<sup>2</sup>
- Includes an advanced security solution with 256-bit AES encryption
- Features a USB Type-C port. Includes a USB Type-C to USB Type-C and USB Type-C to standard USB Type-A cable
- Three-year limited warranty

#### Capacities:

**512GB**  
(up to 550MB/s read, 400MB/s write<sup>1</sup>)

**1TB**  
(up to 550MB/s read, 400MB/s write<sup>1</sup>)

**2TB**  
(up to 550MB/s read, 400MB/s write<sup>1</sup>)

**480GB**  
(up to 500MB/s read, 420MB/s write<sup>1</sup>)

**960GB**  
(up to 500MB/s read, 420MB/s write<sup>1</sup>)



**Store and share quickly with USB 3.1 speeds.** Quickly store and access your content anywhere with the Lexar Portable SSD. This sleek, compact SSD provides impressive performance on the go, with speeds up to 550MB/s read and 400MB/s write—up to four times faster than traditional external hard drives<sup>3</sup>. This makes it easy to quickly access, move, or backup all your favorite movies, music, photos, and files. Available in 512GB, 1TB, 2TB, 480GB and 960GB capacities.

**Sleek, Slimline design and exceptional resilience to the elements.** Showcase your discerning style with the sleek, premium finish of the SL200 Portable SSD. With its small, slim size, you can slip it in your pocket and go. And unlike traditional drives, it has no moving parts, so it provides exceptional resilience to harsh temperatures and vibration<sup>2</sup>. It also includes an LED activity light, so you know when your file transfer is complete.

**Securely protect your files.** Looking to protect personal information, financial records, or other sensitive files on the go? The SL200 SSD includes an advanced security solution with 256-bit AES encryption to help protect your essential files against corruption, loss, and deletion. Easily create a password-protected safe that automatically encrypts data. And for peace of mind, files that are deleted from the safe are securely erased and can't be recovered.

**Rigorously tested.** All Lexar product designs undergo extensive testing in the Lexar Quality Labs, facilities with more than 1,100 digital devices, to ensure performance, quality, compatibility, and reliability.

*For more than 25 years, Lexar has been a trusted leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, solid-state drives and DRAM. With so many options, it's easy to find the right Lexar solution to fit your needs. Lexar products are available worldwide at major retail and e-tail stores. For more information or support, visit [www.lexar.com](http://www.lexar.com).*

## USB 3.1

Lexar Retail Sku	Capacity	Region	Single UPC Code	Inner Carton UPC Code	Inner Carton Qty
LSL200X480G-RNNNG	480GB	Global	843367123438	10843367123435	10
LSL200X960G-RNNNG	960GB		843367123445	10843367123442	
LSL200X512G-RNNNG	512GB		843367121243	10843367121240	
LSL200X001T-RNNNG	1TB		843367121007	10843367121004	
LSL200X002T-RNNNG	2TB		843367121021	10843367121028	
LSL200X512G-RNNNU	512GB	North America	843367121250	10843367121257	
LSL200X001T-RNNNU	1TB		843367121014	10843367121011	
LSL200X002T-RNNNU	2TB		843367121038	10843367121035	

<sup>1</sup> Up to 550MB/s read transfer, write transfer speeds lower. Speeds based on internal testing. Actual performance may vary.

<sup>2</sup> Temperature resistant ( 32°F to 158°F) or (0°C to 70°C) and vibration resistant (7~800Hz, 3.08Grms, 30min/axis(X,Y,Z)) Based on internal testing. Actual performance may vary.

<sup>3</sup> Comparison based on internal testing. Actual performance may vary.  
Lexar is not liable for any loss of data or images.

**NOTE:**

Security safeguards, by their nature, are capable of circumvention. Lexar does not guarantee data will be 100% secure from unauthorized access, alteration, or destruction.

To ensure compatibility and best performance, please visit [lexar.com/downloads](http://lexar.com/downloads) to download the latest USB 3.1 driver.

Product appearance, performance, software offerings, and packaging may vary depending on ship date and available inventory.

Actual usable memory capacity may vary. 1GB equals 1 billion bytes.

[www.lexar.com](http://www.lexar.com)

©2021 All Rights Reserved. Information, products, specifications, and features are subject to change without notice. Neither Lexar nor Longsys is responsible for omissions or errors in typography or photography. Lexar, the Lexar logo, and all other Lexar trademarks are the property of Longsys Electronics (HK) Co., Ltd. or Shenzhen Longsys Electronics Co., Ltd. All other trademarks are property of their respective owners.