

2702482

https://www.phoenixcontact.com/gb/products/2702482

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



LED machine light, 24 V DC, emission angle: 85 °/95 °, length: 540 mm, diameter: 40 mm, degree of protection: IP67, can be swiveled, resistant to coolants and lubricants

Product Description

This LED machine light is designed to provide illumination inside or on machinery. You can use the light in harsh environments. This is possible thanks to the following properties: - High type of protection - Resistance to common cooling agents and lubricants - Resistance to vibrations and shock - 4 mm-thick safety glass The small diameter of just 40 mm enables mounting even where space is at a premium. Mounting is by means of holders or brackets (neither of which are supplied as standard) in which the light can swivel and the lighting can therefore be optimally aligned.

Your advantages

- · Space saving, thanks to the small diameter
- Plug-in supply line enables free choice of the cable length as well as quick and easy installation
- · Focused illumination, thanks to swivel action
- IP67 protection and resistance to cooling agents and lubricants enables use in machine tools
- · Can be used at high temperatures and can be subjected to strong vibrations and shocks
- · Safety glass enables use even in environments with potential mechanical strain
- · ETL approval permits use on the North American market
- · Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 60,000 h

Commercial Data

Item number	2702482
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DRL222
Product Key	DRL222
Catalog Page	Page 505 (C-6-2019)
GTIN	4055626247816
Weight per Piece (including packing)	1,100 g
Weight per Piece (excluding packing)	986 g
Customs tariff number	94054239
Country of origin	DE



2702482

https://www.phoenixcontact.com/gb/products/2702482

Technical Data

Notes

Order information:	The PLD M-ME MC/D40 mounting holder (Item No. 2702491) or the PLD M-ME MB/D40 mounting bracket (Item No. 2702527) is required in order to mount the light.

Product properties

Product type	Light
Mounting position	any
Application	Machine
	Machine tool

Electrical properties

Supply: Module electronics

Connection method	M12 connector (A-coded)
Number of positions	4
Permissible conductor cross section	min. 0.34 mm²
Supply voltage	24 V DC
Supply voltage range	20 V DC 28 V DC
Current consumption	typ. 0.67 A (at 24 V DC)
Power consumption	approx. 16 W (at 24 V DC)
Protective circuit	Surge protection; Varistor and suppressor diode, 36 V DC
	Reverse polarity protection; Polarity protection diode

Connection data

Connection method	M12 connector (A-coded)
-------------------	-------------------------

LED signaling

Light properties

Source of light type	LED
Number of LEDs	42
Service life, lighting appliance	60000 h (L70)
Color temperature	5000 K
Color rendering index	80
Luminous flux	approx. 1680 lm (Net luminous flux)
Luminous efficacy	approx. 105 lm/W
Illumination	max. 732 lx (Distance of 1 m)
	min. 326 lx (Distance of 1 m over 1 m² area)
Average illumination	541 lx (Distance of 1 m over 1 m² area)
Emission angle	85 ° (C0-C180)
	95 ° (C90-C270)
Ordinance	Delegated Regulation (EU) 2019/2015



2702482

https://www.phoenixcontact.com/gb/products/2702482

Energy efficiency class	C (2 light sources)
	E (1 light source)
Note	This product contains energy efficiency class C light sources.
	This product contains an energy efficiency class E light source.

Dimensions

Dimensional drawing	2.13 540 40 40 40 40 40 40 40 40 40 40 40 40 4
Width	40 mm
Height	30 mm
Length	540 mm
Diameter	40 mm
Note on dimensions	Length without M12 flush-type connector

Material specifications

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C 50 °C
Degree of protection	IP67
Air pressure (operation)	69 kPa 102 kPa
Air pressure (storage/transport)	69 kPa 102 kPa
Ambient temperature (storage/transport)	-20 °C 75 °C
Permissible humidity (operation)	95 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)

Standards and regulations

Mounting

Mounting type	Screw mounting
Assembly instructions	Mounting with mounting holders or mounting brackets, please observe the notes in the package slip.
Mounting position	any




2702482

https://www.phoenixcontact.com/gb/products/2702482

Drawings

Dimensional drawing







2702482

https://www.phoenixcontact.com/gb/products/2702482

Approvals



ETLus

Approval ID: LV-Lighting-Systems



cETL

Approval ID: Luminaires



EAC

Approval ID: TR_TS_D_12879-22

cETLus



2702482

https://www.phoenixcontact.com/gb/products/2702482

Classifications

ECLASS

	ECLASS-9.0	27110345	
	ECLASS-10.0.1	27110345	
	ECLASS-11.0	27110345	
ETIM			
	ETIM 8.0	EC000348	
UNSPSC			
	UNSPSC 21.0	32151500	



2702482

https://www.phoenixcontact.com/gb/products/2702482

Environmental Product Compliance

REACh SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"



2702482

https://www.phoenixcontact.com/gb/products/2702482

Mandatory Accessories

Mounting holder

Mounting holder - PLD M-ME MC/D40 - 2702492 https://www.phoenixcontact.com/gb/products/2702492



Mounting holder, for machine lights PLD M 260 .../D40, Swiveling range ±20°

Mounting brackets

Mounting brackets - PLD M-ME MB/D40 - 2702527 https://www.phoenixcontact.com/gb/products/2702527



Mounting brackets, for machine lights PLD M 260 .../D40, Swiveling range ±45°

Accessories



2702482

https://www.phoenixcontact.com/gb/products/2702482

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 1,5-PUR/M12FS - 1668108 https://www.phoenixcontact.com/gb/products/1668108



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: $1.5\ m$

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 3,0-PUR/M12FS - 1668111 https://www.phoenixcontact.com/gb/products/1668111



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: 3 m



2702482

https://www.phoenixcontact.com/gb/products/2702482

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 5,0-PUR/M12FS - 1668124 https://www.phoenixcontact.com/gb/products/1668124



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket straight M12, coding: A, cable length: $5\,\mathrm{m}$

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 1,5-PUR/M12FR - 1668221 https://www.phoenixcontact.com/gb/products/1668221



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M12, coding: A, cable length: 1.5 m



2702482

https://www.phoenixcontact.com/gb/products/2702482

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 3,0-PUR/M12FR - 1668234 https://www.phoenixcontact.com/gb/products/1668234



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M12, coding: A, cable length: 3 m

Sensor/actuator cable

Sensor/actuator cable - SAC-4P- 5,0-PUR/M12FR - 1668247 https://www.phoenixcontact.com/gb/products/1668247



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M12, coding: A, cable length: 5 m

Phoenix Contact 2022 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk