

Single Wire Earpiece with Acoustic Tube

RS Stock number 781-1706



Features:

- Surgical grade acoustic tube; discreet and comfortable
- Quick-fasten secure structure
- Environmental PU cable reinforced with Kevlar
- Optional ear mold allows ambient sounds
- Discreet communication in sensitive environments
- Suitable for many applications including; security personnel, hotel and catering staff, etc.



Technical Specification

Speaker:

Dimensions: Od 19.0mm x 10.6mm
Impedance: $73 \pm 200\Omega$ @ 1000Hz
Rated Input Power: 1mW
Rated Output Power: 300mW
Sound Pressure Level: $117 \pm 3\text{db}$ @1000Hz

Microphone:

Type: Electric Microphone
Impedance: 2.2 k Ohm
Sensitivity: $-40 \pm 3\text{db}$ @1000Hz
(0db = 1V/PA)
Operating Voltage: 1.0-10VDC

PTT:

Dimensions: 34.9 x 14.2 x 11.8mm