

Datasheet

Din Rail Mount Optocoupler, 500mA DC, 5-30VDC

RS Stock number 905-4286



Specifications:

Rated input voltage	5-30V DC
Rated input current	6 mA
Status indicator	LED
Max. switching frequency	100 Hz
Rated switching voltage	3-48V DC
Rated switching current	500mA
Voltage Drop at Max	<1V
Operating Temperature	-25°C to 60°C
Storage Temperature	-40°C to 70°C
Rated impulse withstand voltage	2.5kW
Wire strip length	7 to 9mm
Insulating material	PA
Torque	0.6 Nm
Dimensions (HxWxD)	60.8 x 67.5 x 6.1mm