

## Thermal Transfer Printable Labels



Article No.:030112

Brady Material No.: [B-427](#)

Material Type: Self-laminating Vinyl

Colour: White/Transparent

Order Reference: THT-9-427-10

Size - Height (mm): 36.50

Size - Width (mm): 25.40

Total Qty per Pack: 10000 Label(s) / Pack

Printable Area - Height (mm): 12.70

Printable Area - Width (mm): 25.40

### Specifications for Thermal Transfer Printable Labels

<b>Adhesive</b>	Permanent Acrylic
<b>Application</b>	Voice & Data Communication; Wire & Cable Marking
<b>Approval/Compliance</b>	UL Recognised
<b>Article No.</b>	030112
<b>Brady Material No.</b>	<a href="#">B-427</a>
<b>Material Type</b>	Self-laminating Vinyl
<b>Colour</b>	White/Transparent
<b>Finish</b>	Matt
<b>Horizontal Repeat (mm)</b>	27.31
<b>Description</b>	Printable, self-laminating vinyl labels for thermal transfer printers. Please Note: This material is UL recognised with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
<b>Max. Service Temp. °C</b>	70
<b>Max. Wire/Cable Diameter (mm)</b>	7.60
<b>Min. Wire/Cable Diameter (mm)</b>	3.90
<b>Order Reference</b>	THT-9-427-10
<b>Printable Area - Height (mm)</b>	12.70
<b>Printer Compatibility</b>	BBP12; BBP11; BP1244; BP1344; BP2461; BP3481; BP6441; MVP200; MVP300; 300XPlusII; 360XPlusII; 600XPlusII; PR200Plus; PR300Plus; PR600Plus; IP300; IP600

<b>Ribbon Series</b>	R4300, R7950
<b>Shape</b>	Rectangle
<b>Size - Height (mm)</b>	36.50
<b>Size - Width (mm)</b>	25.40
<b>Additional Information</b>	Self-laminating;Self-extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
<b>Total Qty per Pack</b>	10000 Label(s) / Pack
<b>Vertical Repeat (mm)</b>	41.28
<b>Voice/Data Application</b>	4 Pair UTP;CAT 5;CAT 5E;CAT 6;RG-59 Coax;RG-6 Coax;Silver Satin
<b>Web Width (mm)</b>	85.09
<b>Industry</b>	Data & Telecommunications;Electrical
<b>Min. Service Temp. °C</b>	-40
<b>Printable Area - Width (mm)</b>	25.40
<b>QTY. per Row</b>	3
<b>Thickness (mm)</b>	0.102