

WP-STEEL S 10 - Protective hose



3240686

<https://www.phoenixcontact.com/in/products/3240686>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Stainless steel 1.4301/AISI 304, degree of protection: IP40, color: silver, inside diameter: 8 mm, Total length: 10 m

Commercial data

Item number	3240686
Packing unit	1 m
Minimum order quantity	1 m
Sales key	BF7
Product key	AF7DSA
Catalog page	Page 597 (C-3-2019)
GTIN	4046356736909
Weight per piece (including packing)	999.9 g
Weight per piece (excluding packing)	999.9 g
Customs tariff number	83071000
Country of origin	DE

WP-STEEL S 10 - Protective hose



3240686

<https://www.phoenixcontact.com/in/products/3240686>

Technical data

Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
--------------------	--

Product properties

Product type	Protective hose
Tensile strength GRP	500 N

Dimensions

Internal dimensions

Internal diameter	8 mm
-------------------	------

Material specifications

Material	Stainless steel 1.4301/AISI 304
Components	halogen-free

Cable/line

Bending radius, dynamic	50 mm
Bending radius, static	20 mm
Tensile strength	500 N
Halogen-free	yes

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-200 °C ... 600 °C

WP-STEEL S 10 - Protective hose



3240686

<https://www.phoenixcontact.com/in/products/3240686>

Classifications

ECLASS

ECLASS-11.0	27430301
ECLASS-13.0	27430301
ECLASS-12.0	27430301

ETIM

ETIM 9.0	EC001179
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-STEEL S 10 - Protective hose



3240686

<https://www.phoenixcontact.com/in/products/3240686>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

WP-STEEL S 10 - Protective hose

3240686

<https://www.phoenixcontact.com/in/products/3240686>



Accessories

WP-SC BRASS 10 - Cable protection end sleeve

3241065

<https://www.phoenixcontact.com/in/products/3241065>



Cable protection end sleeve, material: Brass, nickel-plated, color: silver, inside diameter: 8.5 mm

WP-G BRASS IP40 PG7 - Protective hose screw connection

3241037

<https://www.phoenixcontact.com/in/products/3241037>



Cable gland made from brass with Pg thread, IP40 protection

WP-STEEL S 10 - Protective hose

3240686

<https://www.phoenixcontact.com/in/products/3240686>



WP-G BRASS IP40 M10 - Protective hose screw connection

3241044

<https://www.phoenixcontact.com/in/products/3241044>



Cable gland made from brass with metric thread, IP40 protection

WP-GT BRASS PG7 - Protective hose screw connection

3241023

<https://www.phoenixcontact.com/in/products/3241023>



Cable gland made from brass with Pg thread, rotatable, IP40 protection

WP-STEEL S 10 - Protective hose

3240686

<https://www.phoenixcontact.com/in/products/3240686>



WP-GT BRASS M10 - Protective hose screw connection

3241030

<https://www.phoenixcontact.com/in/products/3241030>

Cable gland made from brass with metric thread, rotatable, IP40 protection



WP-BASE HF 9-10 - Hose clamp

3240965

<https://www.phoenixcontact.com/in/products/3240965>

Hose clamp, material: Steel, galvanized, color: black/silver



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in