

Surftest SJ-210 [mm]

"R2µm; 0,75mN"

Item number: 178-560-11D














Description

This is a portable measuring instrument that allows you to easily and accurately measure surface roughness.

The Surftest SJ-210 offers you the following benefits:

- Skid system gives you user friendly and intuitive menu navigation.
- It works independently of mains power, allowing you to make on-site measurements.
- The 6.0 cm [2.4"] colour graphic, back-lit LCD gives you excellent readability.
- · It performs roughness analyses conform to various international standards (EN ISO, VDA, ANSI, JIS) and customized settings.
- Different drivers expanding the range of applications.
- Calculation results, assessed profiles, bearing and amplitude curves can be displayed.
- Support of 21 languages.

Measuring speed:

Operation by keys on the front and under the sliding cover.

Features

Detector measuring force: 0.75 mN 60° Stylus tip angle:

Stylus tip radius: 2 µm 500 g Mass: Measuring range: 16 mm,

4.8 mm [S-type]

Traverse: 17.5 mm, 5.6 mm [S-type]

0.25 mm/s; 0.5 mm/s;

0.75 mm/s

1 m Cable length:

Measuring method: **Differential inductance**

Range: 360 µm Stylus: **Diamond Tip** Skid radius: 40 mm

Roughness Profile (R), R-Motif, Profiles:

DF-Profile and more

Roughness standard: EN ISO, VDA, JIS, ANSI and customize settings

No. of sampling length (L): x 1, x 3, x 5, x L **Gauss, 2CR75, PC75** Digital filter: Cut-off length:

> 0.8 mm; 2.5 mm λs: 2.5 μm; 8 μm

Coloured upper / lower limit Tolerance:

Via AC adapter (DC 7.5 V 1.5 W) built-in or Power supply:

rechargeable battery

λc: 0.08 mm; 0.25 mm;

Functions: Switchable between 16 languages: Japanese,

English, German, French, Italian, Spanish, Portuguese, Czech, Polish, Hungarian,

Turkish, Swedish, Dutch, Korean, Traditional

Chinese, Simplified Chinese

Automatic after 30 seconds Auto-sleep:

Inch-Metric: Metric

Accessories

Optional accessories:





Granite stand for Surftest SJ-210 / SJ-310* 178-029

Suggested retail price: 738.00 €*



Adapter for magnetic stand; D8mm for Surftest SJ-210 / SJ-310 12AAA221

Suggested retail price: 45.00 €*



Standard drive unit 17,5 mm for SJ-210 / SJ-310 series 178-230-3

Suggested retail price: 669.00 €*



S-type drive unit 5,6 mm for SJ-210 / SJ-310 series

Suggested retail price: 2,388.00 €*



S-type drive unit set for SJ-210 / SJ-310 series 178-234-3

Suggested retail price: **2,494.00 €***



R-type drive unit 17,5 mm for SJ-210 / SJ-310 series 178-235-3

Suggested retail price: 1,295.00 €*



Extension rod length 50mm for SJ-210 / SJ-310 series 12AAA210



Suggested retail price: **220.00 €***



Standard detector 2µm; 0,75mN for SJ-210 / SJ-310 series 178-296

Suggested retail price: **594.00 €***



Detector small holes D4,5; 2µm; 0,75mN for SJ-210 / SJ-310 series 178-383

Suggested retail price: **721.00 €***



Detector small holes D2,8; $2\mu m$; 0,75mN for SJ-210 / SJ-310 series 178-384

Suggested retail price: **721.00 €***

« < **1** 2 3 > »