

PRODUCT-DETAILS

F204 A-100/0,3

F204 A-100/0,3 Residual Current Circuit Breaker



General Information

Extended Product Type	F204 A-100/0,3
Product ID	2CSF204101R3900
EAN	8012542918301
Catalog Description	F204 A-100/0,3 Residual Current Circuit Breaker
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Technical

Standards	IEC/EN 61008 UL 1053
Operating Characteristic	Instantaneous
Type of Residual Current	A type
Rated Residual Current	300 mA
Rated Current (I_n)	100 A
Number of Poles	4
Position of Neutral Terminals	Right
Power Loss	at Rated Operating Conditions per Pole 8.2 W
Rated Voltage (U_r)	400 V

Rated Frequency (f)	50/60 Hz
Ambient Air Temperature	Operation -25...55 °C
Connecting Capacity	Busbar 10 mm ² Rigid 35 ...35 mm ² Flexible 35 ...35 mm ²
Degree of Protection	IP2X
Electrical Endurance	10000 cycle
Mounting Type	DIN rail
Object Classification Code	Q
Pollution Degree	2
Rated Conditional Short-Circuit Current (I _{nc})	10 kA
Rated Insulation Voltage (U _i)	500 V
Rated Operational Voltage	230 / 400 V AC
Width in Number of Modular Spacings	4

Environmental

Ambient Air Temperature	Operation -25...55 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC
----------------------------------	-----------------

Dimensions

Product Net Width	0.070 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.380 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	80 mm
Package Level 1 Height	41 mm
Package Level 1 Depth / Length	94 mm
Package Level 1 Gross Weight	0.415 kg
Package Level 1 EAN	8012542918301
Package Level 2 Units	crate 6 piece
Package Level 2 Width	246 mm
Package Level 2 Height	94 mm
Package Level 2 Depth /	80 mm

Length

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
E-Number (Finland)	3259404

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	9AKK107991A6127
RoHS Information	2CSC423001K2702

Popular Downloads

Data Sheet, Technical Information	9AKK107991A8329
Instructions and Manuals	9AKK107991A6127

Classifications

Object Classification Code	Q
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

