

Product data sheet

179 N X-7/137

EAN-No. 4000896224463



137-pieces · 7 Drawers total



Application:

Efficient, mobile organisation of tools

- Tool trolley
- 5 flat and 2 high drawers
- Complete with 137-piece tool assortment in Safety-Insert-System soft foam insert

Work areas

- Much larger storage and work areas in plastic (179N) or stainless steel (179NX)
- Fully sealed work surface protects inside of trolley from leaking liquids
- Interfaces integrated in the work area for accessories such as laptop holders and top modules

Body / Pull-handle

- Extremely robust design thanks to dual-wall structure
- Complete welded construction of the entire body for tough daily workshop use
- Optimised, yielding edge protection on all four corners with real impact protection thanks to internal damping concept
- Ergonomically optimised pull handle for better manoeuvrability

Locking concept

- Ergonomically arranged side lock position for better operability protects keys and lock against damage
- Highly secure closing system with central locking technology for optimum protection of your property
- 2-stage locking
 - Central locking, lockable with cylinder lock and 2 folding keys
 - Mutual drawer locking for minimum tilting risk

Drawer concept

- Self-closing and reciprocal locking of the drawers prevents unwanted opening
- 100% sliding-out with ball-bearing telescopic slides
- Drawer design for optimum use of the interior
- Drawer fronts for optimised handling
- Dirt-resistant drawer coating for easy cleaning

High performance chassis

- Large wheels with high loading capacity, precision ball bearing and dual rounded rim in the pivot bearing, easy manoeuvrability, even with high dynamic load
- 2 swivel castors with dual brake:
 - Braked castors prevent rolling away
 - Braked swivel bearings prevent the swivel castors from turning, e.g. on inclined surfaces
- Protective ring prevents dirt and threads from getting in
- Elastic castors enable smooth movement

Assistant 179N-6 – 9:

- Solvent-resistant plastic work surface

EAN-No. 4000896**224463**



- Metal handle, powder coated in black

Assistant® **179NX-6 – 8:**

- Stainless steel work surface
- Extra protection through high-quality plastic end caps
- Brushed stainless steel handle
- Total loading capacity (dynamic): 540 kg
- Loading capacity (static): 1000 kg
- Loading capacity of high drawer: 25 kg
- Colour: HAZET blue
- Tool trolley Made in Germany
- Dimensions: 785 mm x 518 mm x 1020 mm
- Net weight: 89 kg
- Drawers, flat: 5× 81 x 522 x 398 mm
- Drawers, high: 2× 166 x 522 x 398 mm
- (Drawer) size for plastic drawer insert: 3/3+
- Worktop: Stainless steel
- Number of fixed castors: 2 (Ø 125 mm)
- Number of swivel castors: 2 (Ø 125 mm)
- Number of tools: 137

<

Product data sheet

179 N X-7/137

EAN-No. 4000896224463



811K • ●

1 x 5.5



811KPH • ●

PH2



2105LG/9H • ○



163-374/27



600N • □

6 • 7 • 8 • 9 • 10 • 11 • 12 •

13 • 14 • 15 • 16 • 17 • 18 •

19 • 21 • 22 • 24

630 • □

6 x 7 • 8 x 9 • 10 x 11 •

12 x 13 • 14 x 15 • 16 x 17 •

18 x 19 • 21 x 22 • 24 x 27 •

30 x 32



5000-3CT • □ 1/2

5122-3CT



9012M-1 • □ 1/2