



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	CD with software Communication cable Documentation CD Installation guide Rack mounting hardware Rack mounting brackets Rack mounting support rails USB cable Warranty card
--------------------	--

Physical

Cable length	1.83 m
Number of rack unit	2U
Colour	Black
Depth	50.5 cm
Height	8.5 cm
Net weight	21 kg
Width	43.2 cm

Input

Network frequency	40...70 Hz auto-sensing
Plug standard	BS1363A British IEC 60320 C14 Schuko CEE 7 / EU1-16P
Input voltage limits	50...150 V 40% load 80...150 V
Input voltage	230 V

Output

Rated power in W	1000 W
Maximum configurable power in W	1000 W

Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Outputvolt_other	220 V 240 V
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Nb of power socket outlets	6 IEC 60320 C13
Bypass type	Built-in bypass
Output voltage	230 V

Conformance

Product certifications	CE EAC
------------------------	-----------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-20...50 °C
Storage altitude	0.00...15240.00 m
Acoustic level	50 dBA
Heat dissipation	317 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	1
Number of battery free slots	0
Battery recharge time	3 h
Liquid value	0

Communications & Management

Free slots	0
Control panel	Multifunction LCD status and control console
Alarm	Audible and visible alarms prioritized by severity
Emergency power off	Yes

Surge Protection and Filtering

Surge energy rate	432 J
-------------------	-------

Packing Units

Package 1 Weight	29.6 kg
Package 1 Height	24.6 cm
Package 1 width	59.4 cm
Package 1 Length	74.9 cm
Number of Units in Package 3	12

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---