

Height-adjustable workstation



- ▶ Its aluminum profile structure allows great flexibility and the adaptation of many accessories.
- ▶ Its electrically adjustable feet will allow you to adapt the height of the tray to the operator for better productivity while avoiding musculoskeletal disorders.
- ▶ Delivered as a kit, to assemble yourself
- ▶ Can be associated with workstation accessories available at the catalogue
 - [Ergonomic work chairs](#)
 - [Lighting](#)
 - [Work station accessories](#)

Description

Profile section	45x45L	
Conductivity (ESD)	No	
Workstation width / mm	1500	configurable on request (min/max = 640/2000 mm)
Table height / mm	adjustable height of 730/1140 mm	
Total height / mm	adjustable	configurable on request (min/max = 2300/2700 mm)
Workstation depth / mm	750	configurable on request (min/max = 550/1000 mm)
Table depth / mm	565	configurable on request (min/max = 100/750 mm)

