

#### **FEATURES**

- Recyclable and environmentally friendly
- Heavy duty with reinforced base, sides and stacking rim
- Resistant to most industrial solvents
- Hygienic, clean, smooth inside faces guard against buildup of grease etc
- Available in 7 sizes and 6 colours as standard
- Index card slot for instant product identification

# RS PRO PP Storage Bin Storage Bin, 75mm x 100mm, Black

RS Stock No.: 909-6906



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

From RS Pro range of economy plastic storage bins made from robust recycled polypropylene designed for simple and effective small parts organisation and storage in the workplace and in the home. These storage bins are stackable and can be stacked on top of one another to provide both a space saving solution to your storage needs and ease of handling.

#### **General Specifications**

Material	PP
Colour	Black
Size	Size 2
Application	Home, Office ,Warehouse ,Laboratory Hospital, Garage

#### **Mechanical Specifications**

Volume	1.27 litres
Maximum Container Stack Height	5mm
Maximum Stack Load Capacity	12kg
Weight	8kg

External dimensions								
Dimension	165mm x 100	Omm x 75mm						
Depth	165mm	(Overall)						
Width	100mm	(Overall)						
Height	75mm	(Overall)						
Base Length	143mm	(Overall)						



Internal dimensions						
Dimension	154mm x 88mm x 63mm					
Depth	154mm					
Width	88mm					
Height	63mm					
Base Length	131mm					

## **Operation Environment Specifications**

Operating Temperature Range	-15°C to 50°C
-----------------------------	---------------





4	 -B	-	-	>

	Size 1	Size 2	Size 3	Size 4	Size 5	Size 6	Size 7	
O/A Length mm (A)	90	165	240	350	350	375	520	
O/A Width mm (B)	100	100	150	205	205	420	310	
O/A Height mm (C)	50	75	132	132	182	182	200	
O/A Base Length mm (D)	64	143	200	300	300	310	450	
Internal Length mm (A)	80	154	223	330	330	350	470	3
Internal Width mm (B)	88	88	128	179	177	378	270	- 3
Internal Height mm (C)	42	63	120	117	167	164	188	5
Internal Base Length mm	65	121	100	207	207	205	425	

STACKING (
No. Of Cont
(Black Repr
No. Of Cont

	Internal Height mm (C)	42	63	120	11/	16/	164	188			
STACKING (	Internal Base Length mm (D)	65	131	188	287	287	295	435	5	Size 6	Size 7
No. Of Cont	Volume (Litres)	0.46	1.27	4.6	9.1	12.8	28.3	31.4	)	5	5
(Black Repr	Maximum Container stack height	7	5	4	6	4	8	6	912	9096921	9096924
No. Of Con	Maximum stack load	43		20	25	45	60	43		-	2
(Size 7 Bin I	capacity (kg) See details & image opposite	12	12	30	36	45	60	42		-	4563432