

## FEATURES

- Hexagonal drive type
- BZP galvanised steel
- Generally non-magnetic
- Cannot be hardened by heat treatment
- Supplied in a polypropylene case

## 680 piece Steel Screw/Bolt Kit, 4.2mm, 4.8mm, 5.5mm

RS Stock No.: 395-412



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

**Product Description**

From the trusted professional brand, RS PRO, this set of high-quality hex head self-drilling hexagon drive screws are ideal for many applications. Self-drilling screws are very similar to self-tapping screws, however self-drilling screws have the added feature of a drill point end. Self-drilling screws eliminate the need for a pre-drilled pilot hole as they perform the drilling, tapping and fastening in one action. The hardened steel fixings are generally used when fixing metal to metal or metal to timber.

**General Specifications**

<b>Number Of Pieces</b>	680
<b>Screw/Bolt Type</b>	Self Drilling Screw
<b>Head Shape</b>	Hex
<b>Drive Type</b>	Hexagon
<b>Kit Contents</b>	4.2 x 13 Quantity- 200 4.8 x 16 Quantity- 50 5.5 x 19 Quantity- 80 4.2 x 19 Quantity- 50 4.8 x 19 Quantity- 35 5.5 x 25 Quantity- 100 4.2 x 25 Quantity- 50 4.8 x 25 Quantity- 50 5.5 x 32 Quantity- 30 5.5 x 38 Quantity- 35
<b>Applications</b>	Cladding and roofing, Metal (including steel) and wood frames, Car production lines, Sheet metal work

## Mechanical Specifications

<b>Screw/Bolts Lengths</b>	13mm to 38mm
<b>Thread Size</b>	4.2mm, 4.8mm, 5.5mm
<b>Material</b>	Steel
<b>Finish</b>	Bright Zinc Plated
<b>Screw/Bolt Length Longest</b>	38mm
<b>Screw/Bolt Length Shortest</b>	13mm
<b>Specification</b>	DIN 7981, DIN 7982, DIN 7504



Kit contents							
Size (mm)	Qty.	Size (mm)	Qty.	Size (mm)	Qty.	Size (mm)	Qty.
4.2 x 13	200	4.2 x 19	50	4.2 x 25	50	–	–
4.8 x 16	50	4.8 x 19	35	4.8 x 25	50	–	–
5.5 x 19	80	5.5 x 25	100	5.5 x 32	30	5.5 x 38	35

## 395-412



5.5 x 25 RS 546-5884			
4.2 x 13 RS 546-5806		5.5 x 19 RS 546-5878	
5.5 x 32 RS 546-5890	4.8 x 19 RS 546-5856	4.2 x 19 RS 546-5812	4.8 x 25 RS 546-5862
4.8 x 16 RS 546-5834	5.5 x 38 RS 546-5913		4.2 x 25 RS 546-5828