



182.72.104.66RNA69Nadellager

Needle roller bearings RNA6901-XL (Series RNA69) dimension series 69

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	16 mm
D	24 mm
C	22 mm
r _{min}	0,3 mm
m	31 g Mass
C _r	18100 N Basic dynamic load rating, radial
C _{0r}	21600 N Basic static load rating, radial
C _{ur}	3800 N Fatigue limit load, radial
n _G	23200 1/min Limiting speed
n _B	14300 1/min Reference speed
	G16X24X3 Suitable sealing ring
	SD16X24X3 Suitable sealing ring

