



## 2312K

### Self-Aligning Ball Bearings

#### Parts Number

2312KC3

#### Boundary Dimensions

d	60	mm	Bore diameter
D	130	mm	Outside diameter
B	46	mm	Width
r (min.)	2.1	mm	Chamfer dimension

#### Basic Load Ratings

Cr	97000	N	Basic dynamic load rating
C0r	28300	N	Basic static load rating

#### Speeds

Grease	4300	min-1	Grease lubrication
Oil (Oil-bath)	5300	min-1	Oil-bath lubrication

#### Abutment and Fillet Dimensions

da (min.)	71	mm	Diameter of shaft abutment
Da (max.)	119	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

#### Calculation factors

e	0.4	Constant
Y2	2.4	Axial load Factors
Y3	1.6	Axial load Factors
Y0	1.6	Axial load Factors

#### Mass

Mass approx.	2.49	kg	Mass approx.
--------------	------	----	--------------

#### Associated products

Adapter	H2312X	Adapter
---------	--------	---------

