
Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KAKO06MPX
COUPLING HALF: Coupler
FUNCTION: Single Shut-Off
CONNECTION TYPE: Tube
BODY MATERIAL: Brass
CONNECTION SIZE: 4x6 MM

PRODUCT OVERVIEW

Parker’s Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:
- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

FLOW RATE	165 L/min (air)
LENGTH	34 mm
INTERCHANGE TYPE	European Profile
CONNECTION SIZE	4x6 mm
WEIGHT	0.011 kg
INDUSTRY	Transportation
BRAND	Parker
INDUSTRY	General Industrial
MINIMUM OPERATING TEMPERATURE	-4 °F
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
INDUSTRY	Healthcare & Life Sciences
BRAND	Rectus
DIAMETER	2.7 mm (nominal)
MAXIMUM OPERATING TEMPERATURE	212 °F
PRODUCT SERIES	Series 20
MINIMUM OPERATING TEMPERATURE	-20 °C
APPLICATION	Energy Management
APPLICATION	Medical
VALVE TYPE	Standard Valve

APPLICATION	Food & Beverages
APPLICATION	Trucks & Trailers
FUNCTION	Single Shut-Off
SEAL MATERIAL	NBR
APPLICATION	Electronics
APPLICATION	Textile Machinery
SLEEVE MATERIAL	Brass
VALVE INCLUDED	Yes
PLATING TYPE	Without Surface Treatment
REGION OF ORIGIN	Germany
DIVISION	Low Pressure Connectors Europe Division
MAXIMUM OPERATING PRESSURE	507 psi
HEX SIZE	9 mm (external)
BODY MATERIAL	Brass
COUPLING HALF	Coupler
MAXIMUM OPERATING PRESSURE	35 bar
PRODUCT TYPE	Pneumatic Quick Couplings
OPERATION TYPE	Sleeve
QUANTITY PER BOX	10.0
COMPATIBLE FITTING	Series 20 Plug
CONNECTION TYPE	Tube With hose nut, without spring guard
DIVISION	Low Pressure Connectors Europe Division
PRODUCT STYLE	Quick Connect
TECHNOLOGY	Pneumatics
APPLICATION	Pharma
APPLICATION	Industrial Machinery

MAXIMUM OPERATING TEMPERATURE	100 °C
INDUSTRY	Electronics