



## DWE357K

### Compact Reciprocating Saw

#### Selling Proposition

- Compact Design at only 368mm in length, easy access when cutting in tight areas and more flexibility of applications
- Lightweight and balanced for additional control at only 3.1kg
- 4 position blade clamp allows for flush cutting and increased versatility
- Lever-action keyless blade clamp for quick and easy blade changing
- 1050 watt motor, designed for Heavy Duty applications
- With a 29 mm stroke length & 0-2,800 SPM, the DWE357K delivers excellent cutting performance

#### Standard Equipment

- Heavy duty carrying case

#### Warranty Specifications

- 1 Year Free Service Contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Power Input	1050 Watts
Abgabeleistung	525 Watt
No Load Stroke Rate	0-2800 spm
Stroke Length	29 mm
Max. Cutting Capacity [Wood]	280 mm
Max. Cutting Capacity [Steel Sections & Pipes]	100 mm
Max. Cutting Capacity [PVC]	130 mm
Gewicht	3.1 kg