
Etiketthållare magnetisk 100x38 mm

Artikelnummer	174107	**Antal per säljenhet**	1 Paket
Färg	Mörkblå	**EAN per säljenhet**	4005546109008
Antal per frp	förpackning om 50 styck	**Bruttovikt per säljenhet**	943 G
EAN per basenhet	4005546109008	**Ursprungsland**	DE





Logotyper och priser

DURAPRINT.EU
BROWSER BASED PRINTING

Produktbeskrivning

- Etikettficka med två magnetremsor på baksidan
- Användning på metallytor, till exempel lagerhyllor och metallbehållare
- Av slitstark polypropylenplast, färgad baksida och transparent framsida
- Tålig och lämplig för skannrar
- Snabbt byte av insticksetiketter
- Invändigt format: 100 x 38 mm (B x H)
- Passande utskrivbara etikettark: art.nr 102202

Specifikationer

Utvändig bredd (mm)	113
Utvändig höjd (mm)	53

DURABLE Hunke & Jochheim GmbH & Co. KG
Westfalenstraße 77 – 79 · 58636 Iserlohn · Germany
Phone +49 (0) 2371 662 0 · **Fax** +49 (0) 2371 662 221
Mail durable@durable.de | durable.de

The statements contained herein are for informational purposes only and are true and accurate to the best of our scientific and technical knowledge. This information does not constitute a guarantee or warranty, express or implied, nor does it establish a legally valid contractual relationship. It is the customer's responsibility to determine the suitability of this product for the customer's intended use. DURABLE does not assume any liability for the customer's use of this product or the information contained herein.

TÜVRheinland CERTIFIED
Management System
ISO 14001:2015
ISO 9001:2015
www.tuv.com
ID 0091005181

Etiketthållare magnetisk 100x38 mm

Format / passar format	100 x 38 mm
Format	Liggande
Varumärke	DURABLE
Bredd, inner (mm)	100
Höjd, inner (mm)	38
Öppning	Upptill
Skyddande flik	Nej
Utstansat tumgrepp	Nej
Kan klippas i önskad längd	Nej
Med neutral etikett	Nej
Baksidans färg	Mörkblå
Produktens egenskaper med dokumentet	Kan skannas, skyddar dokumentet
Fastsättning via	2 magnetremsor
Typ av fastsättning	Magnetisk
Typ av etikett	DURAPRINT®

DURABLE Hunke & Jochheim GmbH & Co. KG
Westfalenstraße 77 – 79 · 58636 Iserlohn · Germany
Phone +49 (0) 2371 662 0 · **Fax** +49 (0) 2371 662 221
Mail durable@durable.de | durable.de

The statements contained herein are for informational purposes only and are true and accurate to the best of our scientific and technical knowledge. This information does not constitute a guarantee or warranty, express or implied, nor does it establish a legally valid contractual relationship. It is the customer's responsibility to determine the suitability of this product for the customer's intended use. DURABLE does not assume any liability for the customer's use of this product or the information contained herein.

TÜVRheinland CERTIFIED
Management System
ISO 14001:2015
ISO 9001:2015
www.tuv.com
ID 0091005181