

D-Sub M AWG 22-26 HMC contact Cat.7 mod.



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 200 5576
Specification	D-Sub M AWG 22-26 HMC contact Cat.7 mod.
HARTING eCatalogue	https://harting.com/09932005576

Identification

Category	Contacts
Series	D-Sub
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male

Technical characteristics

Conductor cross-section	0.13 ... 0.33 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 22
Transmission characteristics	Cat. 7 _A
Contact resistance	≤10 mΩ
Mating cycles	≥10,000

Material properties

Surface (contacts)	HMC gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	100
Net weight	0.248 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140229211
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522