

## ENGLISH

Datasheet

Stock No: 499-1950

RS Pro Manual Ball Valve Stainless Steel 3/4 in BSPP



## **Product Details**

## Stainless Steel Quarter-turn L- and T-Port Ball Valves

RS Pro Stainless Steel L and T Port Ball Valves used for controlling flow and are excellent choice for shut-off applications. These ball valves are durable and perform well even after long periods of time. Available in a variety of sizes.

Operating Temperature Range: -15 to +232 C

Pressure Rating WOG: 68 bar

Ball and Stem - AISI 316 Stainless Steel

Gland Nut, Handle, Stop-bolt and Lock Plate - AISI 304 Stainless Steel


Body Seal, Seal, Thrust Washer and Stem Pack Material - PTFE

Handle Washer-Bolt Material - ASTM A36

For "L" port valves see R\$ 4991865, R\$ 499-1871, R\$ 499-1887, R\$ 499-1893

For "T" port valves see RS 499-1938, RS 499-1944, RS 499-1950, RS 499-1966

Operating Temperature Range	to +232°C
Pressure Rating WOG	68 bar
Ball and Stem	AISI 316 Stainless Steel
Gland Nut, Handle, Stop-bolt and Lock Plate	AISI 304 Stainless Steel
Body Seal, Seal, Thrust Washer and Stem Pack Material	PTFE
Handle Washer-Bolt Material	ASTM A36



## **Specifications:**

Threaded Connection	3/4 in BSPP
Attachment Type	Threaded
Body Material	Stainless Steel
Thread Size	3/4in
Maximum Working Pressure	68 bar
Ball Material	Stainless Steel
Thread Standard	BSPP
Handle Material	Stainless Steel