

Datasheet

RS Pro 7094877 Analogue Positive Pressure Gauge Bottom Entry 2.5bar, Connection Size G 1/2 RS Calibration RS Stock No: **342-5806**



Product Details

RS Pro analogue positive pressure gauge bottom entry has a maximum pressure measurement of 2.5 bar with connection size of G 1/2. It is suitable for corrosive environments and gaseous or liquid media that will not destruct the pressure system.

Features and Benefits

- Laminated safety glass window
- 316Ti stainless steel element and movement
- 304 stainless steel case with G 1/2 Inch BSPM connection
- Bottom entry connection
- Ambient operating temperature between -20 and +60°C
- Operating temperature (Medium) of +100°C
- 1.6 Per DIN 16005 accuracy class



ENGLISH

Specifications:

Calibrated	RSCAL
Case Material	Stainless Steel
Connection Size	BSP G 1/2
Gauge Outside Diameter	100 mm
Maximum Operating Temperature	+60°C
Maximum Pressure Measurement	2.5 bar
Minimum Operating Temperature	-20°C
Minimum Pressure Measurement	0 bar
Pressure Gauge Type	Bottom Entry
Suitable For	Liquid, Gas