



**1824
OLIVE**

maximum working pressure

bar
80

MPa
8,0

psi
1160

working temperature



**°C
(Celsius)**
From -40 to 250

**F
(Fahrenheit)**
From -40 to 482

**K
(Kelvin)**
From 233 to 523

body

stainless steel 316L

		ØD (mm)	 (kg)
1824 06 00		6	0,001
1824 08 00		8	0,001
1824 10 00		10	0,003
1824 12 00		12	0,004
1824 16 00		16	0,005

