

Features

- PVC Hook-up Wire
- UL 1061 Equivalent
- Tinned Copper Conductors

RS PRO Hook Up Wire

RS Stock No.: 0266384



Representative Image - Colour will vary

RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Stranded Hook-up Wire designed for the internal cabling of electrical and electronic equipment. Suitable for a broad range of applications from control cabinets to specialist machine tools

Hook-up wire is a flexible cable with a durable PVC protective sheath and tinned copper conductors, available in multiple colours, ideal for colour-coding cable installations.

The cable offers good insulation due to the PVC insulation material and installation is easy and efficient thanks to the flexible layout of the cable.

General Specifications

Conductor	Tinned Copper
Insulation	PVC Semi-Rigid
Insulation Colour	Red
Approximate Diameter	1.22 mm
Number of conductors	1
Conductor cross sectional area	22 AWG
Conductor construction	7 strands of 0.25mm
Length	30 MTRS

Mechanical Specifications

Minimum temperature	-20°C
Maximum temperature	+80°C

Electrical Specifications

Voltage rating	300V
----------------	------