



Foot protection

PHOCEA2 S3S SR

UTILITIES

Non-magnetic low-cut shoe with robust construction, thanks to quadruple stitching



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Dual-density outsole



Performance

- Grip on the ground
- High stability ensured by the sole's grip properties



Durability

- Built to last: 4 stitching, robust materials, front and rear reinforcements

Certifications and norms



EN ISO 20345

S3S CI HI WPA FO A E SR

Applications

- Maintenance
- Petrochemical
- Cleanliness
- Public services
- Water and waste treatment
- Power Energy

Protects against risks



Antistatic



Heat



Shock



Cold



Foot protection

PHOCEA2 S3S SR

UTILITIES

Non-magnetic low-cut shoe with robust construction, thanks to quadruple stitching

Standards - Details

Technical details

Shoe type	Low shoe
Outsole material	PU, 2d
Anti-perforation insert	Metal free
Upper material	Leather
Upper finition material	Croupon, Pigmented, Water repellent
Safety toe-cap	Composite
Lining material	Textile, Mesh polyamid
Footbed material	Polyester, PU
Footbed caracteristic	Cold barrier, Ergonomic, Shock-absorption, Removable, Heat barrier, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	500
Size range	36 → 48



Safety footwear

PHOCEA2 S3S SR

UTILITIES

Non-magnetic low-cut shoe with robust construction, thanks to quadruple stitching

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
PHOC2S3SNO36	Black	36	PHOCEA2 S3S SR	3295249290825	13295249290822	5	1	6.7 kg	57.0 cm	21.0 cm	31.5 cm
PHOC2S3SNO37	Black	37	PHOCEA2 S3S SR	3295249291440	13295249291447	5	1	6.8 kg	57.0 cm	21.0 cm	31.5 cm
PHOC2S3SNO38	Black	38	PHOCEA2 S3S SR	3295249291457	13295249291454	5	1	7.1 kg	57.0 cm	21.0 cm	31.5 cm
PHOC2S3SNO39	Black	39	PHOCEA2 S3S SR	3295249291464	13295249291461	5	1	7.3 kg	57.0 cm	21.0 cm	31.5 cm
PHOC2S3SNO40	Black	40	PHOCEA2 S3S SR	3295249291471	13295249291478	5	1	7.4 kg	57.0 cm	21.0 cm	31.5 cm
PHOC2S3SNO41	Black	41	PHOCEA2 S3S SR	3295249291488	13295249291485	5	1	7.7 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO42	Black	42	PHOCEA2 S3S SR	3295249291495	13295249291492	5	1	8.0 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO43	Black	43	PHOCEA2 S3S SR	3295249291501	13295249291508	5	1	8.4 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO44	Black	44	PHOCEA2 S3S SR	3295249291518	13295249291515	5	1	8.8 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO45	Black	45	PHOCEA2 S3S SR	3295249291525	13295249291522	5	1	9.3 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO46	Black	46	PHOCEA2 S3S SR	3295249291532	13295249291539	5	1	9.45 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO47	Black	47	PHOCEA2 S3S SR	3295249291549	13295249291546	5	1	9.4 kg	59.5 cm	22.5 cm	34.0 cm
PHOC2S3SNO48	Black	48	PHOCEA2 S3S SR	3295249291556	13295249291553	5	1	9.6 kg	68.4 cm	26.6 cm	38.2 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height