

A52.100/S, 0...300°C, 100x8mm

Bimetallic thermometer, for industrial applications A52L

Item number: 3626024

Quantity: 1 pcs.

Order code: A52.100-S-C1N-GD-C100GDZ-Z-ZZZ TD FZZVC-
AZ1ZZZZZ1ZZZZ

Overview: A52.100/S, 0...300°C, 100x8mm

Process connection: G 1/2 B

Neck: 30 mm

flat instrument glass

WIKA Serial number *...*

Details: Bimetallic thermometer, for industrial applications A52L

Specifications according to data sheet: TM 52.01

Accuracy class: class 1 per EN 13190

Case: stainless steel

Stem material: stainless steel

Model: A52.100, nominal size 100, location of stem centre back

Connection design: standard, male thread

Scale range: 0 °C ... 300 °C

Process connection: G 1/2 B

Stem diameter: 8 mm

Insertion length L1: 100 mm

Neck: 30 mm

Window: flat instrument glass

Case: Stainless steel

Ingress protection: IP 43

Manufacturer logo: *WIKA*

Stem material: stainless steel 316SS

serial number on dial: Serial number *...*