

FEATURES

- Ultra slimline and compact body
- The floodlight is made from aluminium and toughened glass
- 110° beam angle
- Adjustable bracket
- The LED bulbs offer a 4000K colour temperature which translates to a cool white light
- An LED luminaire offers up to 90% more energy efficiency than traditional Halogen or incandescent bulbs
- Suitable for outdoor use

RS PRO LED Floodlight, 2 LED, 160 W, 12800 → 14400lm, IP65 85 → 265 V

RS Stock No.: 872-4136



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Our RS Pro floodlights are high powered LED lights that have a brilliant build quality. You can hang them from the wall or ceiling with our included mounting bracket. With a rating of IP65 they are suitable for indoor and outdoor use. Our LED Floodlights also have a brilliant efficiency rating of A+.

General Specifications

Floodlight Type	Outdoor
Number of LEDs	2
Luminosity	12800lm to 14400lm
Lumen Efficiency	>80lm/w to 90lm/w
Light Colour	Cool White
Colour Temperature	6500K
Beam Angle	120°
Case Material	Aluminium
Housing Colour	Black
Applications	Warehouses, Car Parks, Walkways, Construction areas, Parks and gardens, Home security

Electrical Specifications

Wattage	160W
Voltage	85 → 265 V
Frequency Range	50Hz to 60Hz
Lamp Type	LED
Solar Panel	No
Life Hours	50000h
Lamp's Efficiency (%)	>90%

Mechanical Specifications

Dimensions	610mm x 115mm x 292 mm
Height	610mm
Width	115mm
Depth	292mm

Operation Environment Specifications

Operating Temperature Range	-30°C to 60°C
Minimum Operating Temperature	-30°C
Maximum Operating Temperature	60°C

Protection Category

IP Rating	IP65
------------------	------

Approvals

Compliance/Certifications	EN61340
Standards Met	CE, DLC, FCC, RoHS Compliant, UL
EU Energy Efficiency Rating	A+

