

Datasheet

## RS Pro Metal RS Pro Horn Speaker, 30W, IP66

RS Stock No: **535-0316**



### Product Details

RS Pro metal horn speaker is an economically priced and IP66 rated round horn loudspeaker for speech use. It has maximum rated power of 30 W. The speaker is ideal for both indoor and outdoor use.

### Features and Benefits

- 100 V line
- 15 W, 10 W, 5 W, 3 W and 1 W power taps
- Coverage: 130°
- Weather-resistant, IP66 rated
- Fitted with swivel U-bracket



ENGLISH

### Specifications:

Colour	Grey
Depth	263 mm
Diameter	266 mm
Frequency Response	250 Hz to 16 kHz
Housing Material	Metal
Indoor/Outdoor Use	Indoor, Outdoor
IP Rating	IP66
Maximum Frequency Response	16 kHz
Minimum Frequency Response	250 Hz
Nominal Rated Power	30 W
Sound Pressure Level	109 dB
Line Voltage	100 V