

## I-Beam Level Magnetic - 120 cm | I-beam levels



- Lightweight reinforced aluminium frame.
- Magnetic edge allows hands free use when working with metal.
- Accurate to 0.029° (0.0005 "/in, 0.5 mm/ m) in normal and reverse position.
- Pitch vial for easy reading of 1 and 2 degree pitch.
- High contrast vial surrounds for maximised visibility.
- Shock absorbing end caps.

Article Number 4932478566

Handles 2

Length (cm) 120

Magnetic Yes

Pack quantity 1