



TOLERANCES: +/- 0.30 mm (+/- 0.012in)



宣又寬	繪圖	DRA'D BY	日期	DATE	材質	MATE.	圖名TITLE:	圖號DWG NO:	版次REVISID:
		JACKY		2010/1/20	ALUMINIUM ALLOY	ADC-12	HQ025		A

ITEM NO	DESCRIPTION
HQ025	NATURAL ALUMINIUM BOX<WITOUT THE GASKET>
HQ025S	@@ IP67 RATING @@<WITH THE SILICON GASKET>
HQ025EMS	@@ IP67 RATING @@<WITH THE SILICON & SHIELDED GASKET>

**MATERIAL:** ALUMINUM ALLOY #ADC-12

**FINISH:** NATURAL (NO SUFFIX)  
 GRAY (SUFFIX -LG)  
 BLACK (SUFFIX -BK)

- 1) SIX(6) M4 x 20mm (0.787") LG. SCREWS  
 SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ±0.10mm TOLERANCE  
 ALL OTHER DIMENSIONS HAVE ±0.30 mm TOLERANCE



宣又實

繪圖

DRA'D BY

日期

DATE

材質

MATE.

圖名TITLE:

圖號DWG NO:

版次REVISID:

JACKY

2010/1/20

ALUMINIUM ALLOY ADC-12

HQ025

A